Rittal – The System.

Faster - better - everywhere.





SK 3245.810 Blue e+ filter fan

State: 26/11/2025 (Source: rittal.com/uae-en)



SK 3245.810 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20 – $900 \, \text{m}^3\text{/h}$







Features

Model No.	SK 3245.810
Design	wall-mounted EMC
Product description	EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3.
Benefits	Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly
Material	Plastic
Colour	RAL 7035
Supply includes	Complete unit ready to install, including EMC filter mat
Fan	Diagonal, EC motor
Air throughput, unimpeded airflow (with chopped-fibre filter)	At 50 Hz: 931 m³/h

© Rittal 2025

Features

Air throughput with matching outlet filter including chopped-fibre filter	At 50 Hz: 728 m³/h
Rated operating voltage	100 V - 130 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 174.6 W
Rated current max.	At 50 Hz: 2.52 A
Dimensions	Width: 323 mm Height: 323 mm Depth: 156 mm
Installation depth	136 mm
Mounting cut-out	Cut-out width: 292 mm Cut-out height: 292 mm
IP protection category to IEC 60 529	IP51 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood
Protection category NEMA	Type 12 with chopped-fibre filter Type 3, 3R with chopped-fibre filter and hose-proof hood
Note	To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays
Operating temperature range	-25 °C55 °C
Storage temperature range	-25 °C70 °C
Noise level	At 50 Hz: 72 dB(A)
Interfaces	0 - 10 V/PWM input Speed output
Packs of	1 pc(s).
Net weight	3.2
Customs tariff number	84145915
EAN	4028177997820
ETIM 9	EC000320
ETIM 8	EC000320

© Rittal 2025 3

Features

ECLASS 8.0 27180716

Approvals

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025 4