

# Rittal – The System.

Faster – better – everywhere.



## SK 3361.610

## TopTherm wall-mounted cooling unit Blue e

State: 28/06/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3361.610 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".



## Features

Model No.	SK 3361.610
Design	wall-mounted
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Stainless steel 1.4301 (AISI 304)
Colour	RAL 9007
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/60 Hz: 0.87 kW Cooling output L35 L50/60 Hz: 0.51 kW
Rated operating voltage	115 V, 1~, 60 Hz
Rated current max.	At 60 Hz: 6.63 A
Start-up current max.	At 60 Hz: 11.5 A
Air throughput (unimpeded air flow)	External circuit: 480 m <sup>3</sup> /h Internal circuit: 600 m <sup>3</sup> /h

# Features

---

Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 60 Hz: 1.58
--	--

---

Design	wall-mounted
--------	--------------

---

Dimensions	Width: 280 mm Height: 550 mm Depth: 280 mm
------------	--

---

Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
-----------------------------------	--

---

Protection category NEMA	UL Type 12
--------------------------	------------

---

Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.26 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.16 t
----------------------------	--

---

Temperature control	e-Comfort controller (factory setting +35 °C)
---------------------	---

---

Operating temperature range	10 °C...55 °C
-----------------------------	---------------

---

Operating temperature max @60 Hz	52 °C
----------------------------------	-------

---

Storage temperature range	-40 °C...70 °C
---------------------------	----------------

---

Setting range	20 °C...52 °C
---------------	---------------

---

Power consumption Pel	Power consumption L35 L35/60 Hz: 0.55 kW Power consumption L35 L50/60 Hz: 0.6 kW
-----------------------	---

---

Permissible operating pressure (p. max.)	28 bar
--	--------

---

Pre-fuse	Miniature circuit-breaker/fuse: 10 A
----------	--------------------------------------

---

Packs of	1 pc(s).
----------	----------

---

Net weight	21.546 kg
------------	-----------

---

Gross weight	22.68 kg
--------------	----------

---

Customs tariff number	84158200
-----------------------	----------

---

ETIM 9	EC000855
--------	----------

---

ETIM 8	EC000855
--------	----------

---

# Features

---

ECLASS 8.0	27180704
------------	----------

---

Product description	SK Cooling unit Blue e, wall-mounted, 0.75 kW, 115 V, 1~, 60 Hz, stainless steel, WxHxD: 280 x 550 x 280 mm
---------------------	---

# Approvals

---

Approvals	UL + C-UL (listed) UL + C-UL - FTFA UR + C-UR (recognized)
-----------	--

---

Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK
--------------	---