Rittal – The System.

Faster – better – everywhere.





SV 3433.040 Bus-mounting fuse base

State: 16/10/2025 (Source: rittal.com/uae-en)



SV 3433.040 - Bus-mounting fuse base

3-pole, for 60 mm bar centre distance.

Features

Model No.	SV 3433.040
Design	Easy Connect
Material	Bus-mounting fuse base: Fibreglass-reinforced, thermoplastic polyester (PBT) Contact hazard protection: Polyamide Fire protection corresponding to UL 94-V0 Contact hazard protection: Polyamide
Colour	RAL 7035
Supply includes	Pre-configured element ready for connection including cover plate, contact hazard protection and exterior connection clamps
Note	Wire end ferrules should be used with fine wire conductors
For bar systems with centre-to- centre spacing	60 mm
Type of electrical connection	Box terminal
Fuse inserts	D III-E 33 (adaptor screw)
Rated insulation voltage	690 V
Rated current max.	63 A
Rated operating voltage	690 V (DC) 690 V, 3~
Note	For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3)
Dimensions	Width: 71 mm Height: 251 mm
Connection of round conductors	1.5 - 16 mm²
To fit busbars	Height: 5, 10 mm
Number of poles	3-pole

© Rittal 2025

Features

Rated operating voltage (L1 + L2)	690 V (DC)
Rated operating voltage (L1 + L3)	690 V (DC)
Packs of	5 pc(s).
Net weight	2
Gross weight	2.496
Copper weight (kg per piece)	0.119
Customs tariff number	85369095
EAN	4028177675018
ETIM 9	EC001644
ETIM 8	EC001644
ECLASS 8.0	27142120

Approvals

Approvala	ADC
Approvals	ABS DNV-GL
	Lloyds Register of Shipping
Explanations	Declaration of conformity

© Rittal 2025 3