

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.318 Thread tapping option

State: 19/08/2025 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.318 - Thread tapping option for Perforex LC 3030

Thread tapping option for Perforex laser centre LC including thread tappers and clamping jaws for M3 – M10.



## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4050.318  |
| Design                   | Movable tool magazine with 6 magazine slots<br>Tool holder<br>Additional drive unit  |
| Product description      | Thread tapping option for cutting threaded holes with the Perforex laser centre LC.  |
| Benefits                 | Machining of projects with tapped holes supported<br>Fast, automatic changeover from laser function to thread-tapping function by accommodating an additional machine head |
| Supply includes          | Thread tapper<br>Clamping units for M3 – M10   |
| Machinable height (max.) | 600 mm   |
| Material thickness       | 5 mm   |
| To fit Model No.         | 4050330  |
| Packs of                 | 1 pc(s).   |
| Net weight               | 78   |
| Gross weight             | 78   |
| Customs tariff number    | 84669360   |
| EAN                      | 4028177806658  |
| ECLASS 8.0               | 36600890   |