

Rittal – The System.

Faster – better – everywhere.



AS 4050.737 Wire end ferrules

State: 05/06/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.737 - Wire end ferrules loose

With plastic collar.

Features

Model No.	AS 4050.737
Design	for manual wire processing for Wire Terminal WT C fully automated wire processing machine
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	12 mm
AWG	20
Internal diameter	2.6 mm
For cross-section	0.5 mm ²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
To fit Model No.	4051.205 4051.210
Delivery form	Loose (10 packs of 100)
Packs of	1,000 pc(s).
Net weight	1 kg
Gross weight	0.105 kg
Customs tariff number	85369010

Features

ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules for wire processing, 0.5 mm ² , white, loose, 12 mm, 10x100

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------