

Rittal – The System.

Faster – better – everywhere.



DK 7111.214

**Cable routing bars, 482.6 mm (19")
attachment**

State: 21/06/2026 (Source: rittal.com/uae-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7111.214 - Cable routing bars, 482.6 mm (19") attachment

For structured routing of entire cable bundles, 482.6 mm (19") attachment, connection comb.



Features

| | |
|-------------------------|--|
| Model No. | DK 7111.214 |
| Product description | For structured routing of entire cable bundles, the cable bars may be secured to a variety of different positions inside the enclosure. |
| Applications | For horizontal cable routing within the distributor level. Thanks to their open mounting holes, they can also be retrospectively slotted onto the 482.6 mm (19") system punchings of the mounting level at any time and secured with the existing mounting screws of the installed components. |
| Material | Support: Sheet steel Cable routing bars, connection combs: Plastic UL 94-V0 |
| Colour | RAL 9005 |
| Supply includes | Cable routing bars Connection combs |
| Number connection combs | 5 |
| Note | Size of individual chambers (WxD) approx. 34 x 100 mm |
| Units | 1 U |
| Packs of | 10 pc(s). |

Features

| | |
|-------------------------------|--|
| Net weight | 0.57 kg |
| Gross weight | 0.668 kg |
| PCF per pack (cradle-to-gate) | 2.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |
| Product description | DK Cable routing bars, 482.6 mm (19") attachment, 1 U |

Tender text

Cable bracket for 482.6mm (19") system punchings, 1 U

1 U single bracket element for horizontal cable guiding directly on the 482.6mm (19") distribution level. The bracket elements allow themselves to be slid back on the 482.6mm (19") system punchings through their open mounting holes at any time and to be fixed with the available securing screws of the mounting components. An extension of existing units through baying by means of connecting piece is possible. For this the connecting piece is put between two bracket elements and thus connects the elements by forming an additional guide chamber between the bracket elements. The connecting pieces needed for baying are contained within the units. delivery scope. The single bracket has a height of approx one height unit (44.45 mm) and thus enables the U related cable feed of whole cable bunches.

Each individual cable bracket can be opened selectively and independently of the others and closed again by means of a turning catch. It thus enables straightforward structuring of the cabling and also flexible change to it

Support element sheet steel, spray finished
Cable feed brackets, connecting pieces, turning catches, plastic