

# Rittal – The System.

Faster – better – everywhere.



## DK 5301.437

## Sheet steel glazed door, vertically divided

State: 20/07/2025 (Source: [rittal.com/uae-en](https://www.rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5301.437 - Sheet steel glazed door, vertically divided for VX IT

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.



## Features

|                     |   |
|---------------------|---|
| Model No.           | DK 5301.437   |
| Product description | To replace existing doors. With underlaid viewing panel and 4-point locking rod. The divided design allows room-optimised siting of the enclosures coupled with the best possible access, thanks to a reduced distance between the individual bayed enclosure suites. |
| Material            | Frame: Sheet steel<br>Viewing window: Single-pane safety glass, 3 mm  |
| Surface finish      | Powder-coated   |
| Colour              | Frame: RAL 7035<br>Comfort handle VX, hinges: RAL 9005  |
| Supply includes     | Door, vertically divided, with comfort handle VX for semi-cylinders with security lock 3524 E, right<br>4 x 180° hinges, fitted on each half of the door<br>Assembly parts  |

# Features

|                                     |  |
|-------------------------------------|--|
| Assembly instruction                | For a door opening angle of 180° when baying, a 180° baying hinge is required                                  |
| Note                                | Door opening angle for stand-alone siting: max. 240°<br>Door opening angle when baying: max. 160°              |
| IP protection category to IEC 60529 | IP 55  |
| To fit                              | Enclosure type: VX IT<br>Width: = 800 mm<br>Height: = 2,000 mm   |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 32.7   |
| Gross weight                        | 33.2   |
| PCF per pack (cradle-to-gate)       | 126.5 kg CO2 eq (Cat B)  |
| Note on PCF category                | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| EAN                                 | 4028177955035  |
| ETIM 9                              | EC000747   |
| ECLASS 8.0                          | 27182204   |