

# Rittal – The System.

Faster – better – everywhere.



## VX 5302.157

# 482.6 mm (19") mounting angles, dynamic

State: 04/04/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5302.157 - 482.6 mm (19") mounting angles, dynamic for VX IT

Mounting angles, also for accommodating server system installation kits.

## Features

Model No.	VX 5302.157
Product description	Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design can directly accommodate all commercially available mounting kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings.
Benefits	Integral, bidirectional U labelling Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling
Technical specifications	Side punchings, round and square, on a U pitch pattern Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components 482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E
Applications	For mounting a 482.6 mm (19") mounting level within the VX IT rack system
Material	Sheet steel, 2.5 mm
Surface finish	Primed
Colour	RAL 9005
Supply includes	Assembly parts
Mounting position	rear
Installation options	Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected

# Features

---

Assembly instruction	To be combined with cross-member, depth stays or mounting bracket for attachment Use of the different mounting options depends on the relevant enclosure dimensions
To fit	Height: = 47 U
Packs of	2 pc(s).
Net weight	14.4 kg
Gross weight	14.9 kg
PCF per pack (cradle-to-gate)	56.8 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	Mounting angles dynamic, 482.6 mm (19") for VX IT, to build an inch-based mounting level within the VX IT housing system, for enclosure height 47 U, sheet steel, 2.5 mm, primed, RAL 9005

# Approvals

---

Explanations	Manufacturer's declaration
--------------	----------------------------