


# Rittal – The System.

Faster – better – everywhere.



## DK 7816.362

## Sheet steel door, vertically divided, solid

State: 20/12/2025 (Source: [m/uae-en](#))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7816.362 - Sheet steel door, vertically divided, solid for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

## Features

Model No.	DK 7816.362
Product description	With 130° hinges and locking rod, including comfort handle for profile half-cylinders with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.
Material	Sheet steel
Supply includes	Assembly parts
Note on Model No.	Without tubular door frame. Tubular door frame available on request.
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: DK-TS Width: 600 mm Height: 2,200 mm
Packs of	1 pc(s).
Net weight	28.69
Gross weight	30.2
Customs tariff number	94032080
EAN	4028177330504
ECLASS 8.0	27182204

## Tender text

Sheet steel door, vertically divided for TS

W x H = 600 x 2200 mm

Sheet steel door with 130° hinges and assembly parts,  
locking rod including comfort handle for semi-cylinder  
with 3524 E security lock.

Non-vented sheet steel door.

Material: Sheet steel, spray finished in RAL 7035

For 600 mm x 2200 mm enclosures