
Rittal – The System.

Faster - better - everywhere.





DK 7979.821 PDU UK, metered version

State: 07/12/2025 (Source: rittal.com/uae-en)



DK 7979.821 - PDU UK, metered version

The power distributor is specifically designed for data centres and free-standing racks with UK (BS 1363) connectors.







Features

Model No.	DK 7979.821	
Design	482.6 mm (19") version	
Product description	High-end power distribution in a compact design for IT network and server racks. Depending on the design, they come with an extensive range of management functions for energy measurement and monitoring.	
Benefits	Tool-free divider kit for VX IT Power-saving design, minimal intrinsic power consumption	
Technical specifications	Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white) Compact circuit-breaker (16 A - Carling type)	
Product modification	Minimum order volume 5 units	
Material	Aluminium section, black anodised Slots: Plastic	
Supply includes	Assembly parts	

© Rittal 2025

Features

Type 3 overvoltage protection with interchangeable arresters while operational, with status monitoring, suitable for integration into PDU enclosure CMC III CAN bus sensors may be connected for ambient monitoring, max. 16 sensors Dimensions Width: 44 mm Depth: 70 mm Length: 1,295 mm No. of sockets and type 16 x BS 1363 Sockets 16 x BS 1363 Sockets 16 x BS 1363 Rated current (max.) 13 A Power consumption 3 kW Infeeds Oty.: 1 Phases per infeed: 1~ Length of connection cable 3 m Type of electrical connection UK Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range 5 °C50 °C Ambient humidity (non-condensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990 EAN 4028177948624			
Depth: 70 mm Length: 1,295 mm No. of sockets and type 16 x BS 1363 Sockets 16 x BS 1363 Rated current (max.) 13 A Power consumption 3 kW Infeeds Qty.: 1 Phases per infeed: 1~ Length of connection cable 3 m Type of electrical connection UK Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 62053-21 Operating temperature range 5 °C50 °C Ambient humidity (non-condensing) 1095 % Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Options	operational, with status monitoring, suitable for integration into PDL enclosure CMC III CAN bus sensors may be connected for ambient	
Sockets 16 x BS 1363 Rated current (max.) 13 A Power consumption 3 kW Infeeds Qty.: 1 Phases per infeed: 1~ Length of connection cable 3 m Type of electrical connection UK Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range 5 °C50 °C Ambient humidity (noncondensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Dimensions	Depth: 70 mm	
Rated current (max.) Power consumption 3 kW Infeeds Qty.: 1 Phases per infeed: 1~ Length of connection cable 3 m Type of electrical connection UK Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range 5 °C50 °C Ambient humidity (noncondensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	No. of sockets and type	16 x BS 1363	
Power consumption 3 kW Infeeds Qty.: 1 Phases per infeed: 1~ Length of connection cable 3 m Type of electrical connection UK Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range 5 °C50 °C Ambient humidity (noncondensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Sockets	16 x BS 1363	
Infeeds Qty.: 1 Phases per infeed: 1~ Length of connection cable 3 m Type of electrical connection UK Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range 5 °C50 °C Ambient humidity (non- condensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Rated current (max.)	13 A	
Phases per infeed: $1 \sim$ Length of connection cable 3 m Type of electrical connection UK Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range $5 ^{\circ}$ C50 $^{\circ}$ C Ambient humidity (noncondensing) Storage temperature range $-25 ^{\circ}$ C70 $^{\circ}$ C To fit Enclosure type: VX IT enclosure frame: $\geq 1,800 \text{mm}$ Enclosure type: VX IT 19" mounting angles: $\geq 1,800 \text{mm}$ Packs of $1 \text{pc}(s)$. Customs tariff number 85366990	Power consumption	3 kW	
Type of electrical connection Directives EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU Standards EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range 5 °C50 °C Ambient humidity (noncondensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Infeeds	•	
Directives	Length of connection cable	3 m	
Low Voltage Directive 2014/35/EUStandardsEN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21Operating temperature range $5 ^{\circ}$ C50 $^{\circ}$ CAmbient humidity (noncondensing) $1095 ^{\circ}$ CStorage temperature range $-25 ^{\circ}$ C70 $^{\circ}$ CTo fitEnclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mmPacks of1 pc(s).Customs tariff number85366990	Type of electrical connection	UK	
EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 Operating temperature range $5 ^{\circ}$ C50 $^{\circ}$ C Ambient humidity (noncondensing) Storage temperature range $-25 ^{\circ}$ C70 $^{\circ}$ C To fit Enclosure type: VX IT enclosure frame: $\geq 1,800 \text{mm}$ Enclosure type: VX IT 19" mounting angles: $\geq 1,800 \text{mm}$ Packs of $1 \text{pc}(\text{s})$. Customs tariff number 85366990	Directives		
Ambient humidity (non-condensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: \geq 1,800 mm Enclosure type: VX IT 19" mounting angles: \geq 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Standards	EN 61000-3 EN 61000-4 EN 61000-6	
condensing) Storage temperature range -25 °C70 °C To fit Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Operating temperature range	5 °C50 °C	
To fit Enclosure type: VX IT enclosure frame: \geq 1,800 mm Enclosure type: VX IT 19" mounting angles: \geq 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990		1095 %	
Enclosure type: VX IT 19" mounting angles: \geq 1,800 mm Packs of 1 pc(s). Customs tariff number 85366990	Storage temperature range	-25 °C70 °C	
Customs tariff number 85366990	To fit	• •	
	Packs of	1 pc(s).	
EAN 4028177948624	Customs tariff number	85366990	
	EAN	4028177948624	

Features

ETIM 9	EC000330	
ETIM 8	EC002762	
ECLASS 8.0	27142604	

Approvals

Approvals	TÜV
Explanations	Declaration of conformity

© Rittal 2025

Tender text

Compact power distributor for deployment in IT server and network enclosures. Vertical installation in the Zero-U space using the supplied universal brackets for common IT racks. Suitable for tool-free quick assembly in the Rittal VX IT and TS IT racks using the special supplied plug-%-play fastener. Robust aluminium housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19 as well as CEE 7/3 (earthing-pin) and BS 1363 (UK), depending on the type (see below for details). The IEC C13 / C19 output slots can be protected with a lock against unintentional removal of the connectors. Unused slots can be closed with slot covers available as accessories. This precludes an unintentional overloading of individual phases an circuits. The fuse circuits and phases are colour-coded for multiphase PDU variants. A fixed-mounted connection cable with IEC C20 or CEE connector appropriate for the variant makes the PDU available for immediate deployment.

The PDU metered has extensive measurement functions for the current and power monitoring of each phase. The integral TFT colour display anables the basic configuration setting and quick access of the electrical consumption data. Two Gigabit network interfaces and the integrated Web server allow access and data transmission using various protocols. The consumption parameters can be forwarded to a DCIM software via SNMP, OPC-UA, Modbus/TCP. For monitoring the ambient parameters, up to 16 sensors (for example temperature / humidity / smoke / leakage / access) as well as VX IT and TS IT handle systems from the CMC accessories program can be connected to the CAN sensor interface.

Optinally, an overvoltage protection module (type3) can be placed on the PDU at the infeed; the overvoltage protection module is equipped with arrestors that can be replaced during operation. For intelligent PDUs, the status is monitored via the network interface, the PDU basic has a floating alarm contact for monitoring the

overvoltage protection. As option, intelligent PDU variants can be supplied with an AC/DC sensitive residual current measurement (RCM type B) with up to 6 measurement points. This changes the PDU length and the number of installed slots for each standard length.

The warranty for proper operation is 24 months.

Technical specifications metered

Input voltage range (L/N/PE): 230 VAC, 50-60Hz

input current: 16A No. of phases: 1

Marking of phases (3-phase PDU only L1, L2, L3):

Rittal Power Pink, black, white

Number of slots type BS1363 (total): 16

Number of slots type IEC 60320/C19 (total): -

No. of circuit brakers: -

Hydraulic-magnetic protective circuit-breaker: 16 A

Connector PDU input: BS1363 Length of connection cable: 3m Connection cable type: H05-VV

No. of wires: 3

Cable cross-section: 1,5mm²
PDU housing width: 44mm
PDU housing depth: 70mm
PDU housing height: 1295mm

PDU material: Aluminium, anodised, in RAL 9005 (black)<(>,<)>

other colours available on request

PDU mounting adaptor (VX IT / TS IT) - Mounting options:

Frame + Zero-U space + cable route

Measurement functions: Measurement per phase or infeed

Values recorded (per phase):

Voltage (V), current (A), frequency (Hz), Power factor<(>,<)>

active energy (kWh), apparent power (kVA)

Active power(kW),neutral conductor current measurement<(>,<)>

fuse monitoring (at 32 A)

Optional: Residual current monitoring (RCM)

AC + DC (RCM Typ B)

max. 6 measurement points per PDU possible

(input / per phase / per fuse)

0 mA - 100 mA je RCM

Voltage measurement range: 90 - 255 V

Voltage resolution: 0.1 V Voltage accuracy: 2%

Current measurement range: 0 - 32 A

Current resolution: 0.1 A Current accuracy: 2% Frequency accuracy: 2%

Active power (kW) accuracy: 2% Apparent power (kVA) accuracy: 2% Active energy (kWh) accuracy: 1%

Power factor accuracy: 2%

Freely settable limit values per slot

for (warning/alarm): Voltage, current, power: yes

Operating hours meter: Yes

Display: TFT, RGB 128x128 pixels

Network interface: 2x RJ45, per 10/100/1000 MBit/s

Network interface: RJ45, integral web server

Supported protocols:

HTTP, HTTPS, SSL, SSH, NTP, Telnet

TCP/IP v4 and v6, DHCP, DNS, NTP, Syslog

SNMP v1, v2c und v3, XML

FTP/SFTP (update/file transfer)

E-mail forwarding (SMTP)

User administration including rights management: Yes

LDAP(S)/Radius/Active Directory connection: Yes

USB port for firmware update+data logging functions: Yes

CAN bus interface: RJ45, for connecting 16 sensors

CAN sensor types: Temperature<(>,<)>

temperature/humidity (combined),infrared access sensor<(>,<)>

leakage, NH measurement module, smoke alarm, vandalism<(>,<)>

airflow, EFD, differential pressure,

VX IT / TS IT handle system

Plug & play drivers - Rittal RiZone DCIM software: Yes

Digital input: 1

Alarm relay: 48 V DC/2 A Acoustic signal encoder

Serial interface Conformity: CE

Standards:

Safety: EN 62368

EMV:

EN 55022 / B

EN 61000-4-2

EN 61000-4-3

EN 61000-6-2 EN 61000-6-3

Safety Directive: 2014/35/EU EMC Directive: 2014/30/EU MTBF (at 40°C) 100.000 hours

Protection category: IP 20 (EN 60529)

Protection class: Class 1

Pollution degree: 2 Overvoltage category: II

Environmental properties: 2011/65/EU (RoHS 2), WEEE

Storage temperature: -20 °C to +70 °C Ambient temperature: +5°C to +50°C

Ambient humidity 10 - 95% rel. humidity, non-condensing Operating altitude (max. above mean sea level): 3000 m

Connector lock for C14 and C20 connectors:

1x (further connector locks optional - DK 7979.020) Covers C13 (optional accessory): DK 7955.010 Covers C19 (optional accessory): DK 7955.015

Warranty: 24 months

Type: Rittal PDU metered, Model No.: DK 7979.821