



# VX 8100.700 - Transport castors for base/plinth system

## VX

For locating onto the base/plinth corner piece 100 or 200 mm high.

## Features

Model No.	VX 8100.700
Product description	For locating onto the base/plinth corner piece 100 or 200 mm high.
Colour	RAL 9005
Supply includes	4 twin castors, 2 x with, 2 x without locks
Clearance floor	100 mm
Load capacity	Max. dynamic load when using 4 twin castors (single enclosure): 3000 N
Weight/pack	8.38 kg
Packs of	4 pc(s).
Net weight	7.98 kg
Gross weight	8.38 kg
Customs tariff number	83024900
ETIM 9	EC002621
ETIM 8	EC002621
ECLASS 8.0	27189262
Product description	VX Transport castors, 2 each with/without lock