


Rittal – The System.

Faster – better – everywhere.



SV 9345.035 Fuse holders

State: 21/05/2024 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.035 - Fuse holders

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

Features

Model No.	SV 9345.035
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection for round conductor cross-sections	AWG 1 - 14
For fuse type (class)	J
Rated operating current max.	60 A
Fuse standard	UL 248-8
Note	For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports)
Test specification	UL 4248-1 UL 4248-4 UL 4248-8
Dimensions	Width: 120 mm Height: 118 mm
Connection for round conductor cross-sections	2.5 - 50 mm ²
To fit fuses	Diameter: 27 mm Length: 60 mm
Voltage range for indicator lights	110 - 600 V
Rated operating voltage	600 V, 3~
Electrical ratings UL (SCCR)	200 kA - 600 V, Fuse Class J max. 60 A, JDDZ/7
Number of poles	3-pole

Features

Packs of	2 pc(s).
Weight/pack	1.256 kg
Copper weight (kg per piece)	0.118
Customs tariff number	85361050
EAN	4028177805408
ETIM 7.0	EC001900
ECLASS 8.0	27400613

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity