


Rittal – The System.

Faster – better – everywhere.



RX 9360.720

RiLineX component adaptor

State: 16/12/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.720 - RiLineX component adaptor

RiLineX component adaptor (25 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



Features

Model No.	RX 9360.720
Design	With connection cable
Benefits	For mounting equipment for top hat rail installation, e.g. motor starter Pre-assembled connection cable Simple clip locking for support rails Optional anti-slip guard Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Simple assembly Coordinated accessories reduce the number of different items required
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 12
Rated current of round conductor	25 A
Rated current of round conductor (UL)	25 A

Features

Electrical ratings UL (SCCR)	5 kA - 600 V, RMS, unprotected 100 kA - 600 V, Fuse Class RK5 max. 30 A, JDDZ/7 50 kA - 480 V, circuit breaker max. 22 A, DIVQ/7 65 kA - 480 V, Combination Motor Controller max. 16 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 12.5 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 40 A, NKJH/7
Cable outlet	Top
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	160 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C

Features

Ambient humidity (non-condensing)	10...90 %
Packs of	4 pc(s).
Net weight	1.36
Gross weight	1.39
Copper weight (kg per piece)	0.096
Customs tariff number	85369095
EAN	4028177997028
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity