

**Rittal – The System.**

Faster – better – everywhere.



**RX 9362.035**

**RiLineX NH fuse-switch  
disconnect**

State: 11/07/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.035 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm<sup>2</sup>. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



## Features

Model No.	RX 9362.035
Design	For 60 mm busbar systems with electronic fuse monitoring
Benefits	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Material	Polyamide (PA 6) Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	RAL 9005 RAL 35745
Supply includes	Connectors for electronic fuse monitoring

# Features

For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
Fuse inserts	NH 00 NH 000
Rated insulation voltage $U_i$	1,000 V
Rated operating voltage	690 V AC
For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 229.5 mm Depth: 104.5 mm
Operating temperature range	-5 °C...35 °C
Storage temperature range	-25 °C...70 °C
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
To fit busbar system	RiLineX RiLine60
Number of poles	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Contamination level	3
with electronic fuse monitoring	Yes
IP protection category to IEC 60529	IP 2XB
Fire load	16.6 MJ/m <sup>2</sup>

# Features

Connection of round conductors, fine wire without wire end ferrule	1.5 - 95 mm <sup>2</sup>
Connection of round conductors, fine wire with wire end ferrule	1.5 - 95 mm <sup>2</sup>
Heat loss max.	22 W
Heat loss per fuse insert (max.)	12 W
Packs of	1 pc(s).
Net weight	1.155 kg
Gross weight	1.175 kg
Copper weight (kg per piece)	0.409
PCF per pack (cradle-to-gate)	7.86
Customs tariff number	85369095
ETIM 9	EC001040
Product description	RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm <sup>2</sup> . Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration