Rittal - The System.

Faster – better – everywhere.





VX 8660.021

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 04/11/2025 (Source: rittal.com/uae-en)

CLOSURES >> POWER DISTRIBUT


CLIMATE CONTROL

INFRASTRUCTURE

SOFTWARE & SERVICES

VX 8660.021 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, sheet steel

Base/plinth corner pieces with trim panels for flexible cable entry.







Features

Model No.	VX 8660.021
Benefits	Reliable – Excellent stability of the base/plinth
	Flexible – Countless interior installation options with VX accessories
	Simple – Flush termination between the baying points
Material	Base/plinth corner piece: Sheet steel
	Base/plinth trim panel front/rear: Sheet steel
	Corner and baying cover: Plastic
Colour	RAL 9005
Supply includes	4 corner covers
	Assembly parts
	4 base/plinth corner pieces, 200 mm high
	1 base/plinth trim panel, front/rear, 200 mm high
	2 base/plinth trim panels, front/rear, 100 mm high
Note	Side base/plinth trim panels finish off a base/plinth unit or provide
	additional stabilisation between base/plinths or enable interior
	configuration of the base/plinth

© Rittal 2025

Features

Dimensions	Height: 200 mm
To fit	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Width: = 400 mm
Type rating to UL 50E	Type 1
	Type 12
Weight/pack	5.85 kg
Packs of	2 pc(s).
Net weight	5.846
Gross weight	5.85
PCF per pack (cradle-to-gate)	22.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177978126
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration