Rittal – The System.

Faster – better – everywhere.





KEL 9408.600 Ex enclosures

State: 10/12/2025 (Source: rittal.com/uae-en)



KEL 9408.600 - Ex enclosures stainless steel, empty enclosure with hinged door

Ex enclosure with hinged door, stainless steel







Features

Model No.	KEL 9408.600
Design	Ex enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C+80 °C
	The specified temperatures may be limited by the installed equipment
	Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Sheet steel
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure Door Mounting plate

© Rittal 2025

Features

Width: 800 mm
Height: 1,000 mm
Depth: 300 mm
739 mm x 955 mm
Yes
Yes
Stainless steel 1.4301 (AISI 304)
Lock version: Cam
Number of locks: 2
Lock insert: 3 mm double-bit
IP 66
NEMA 4X
Type 1
Type 4
Type 4X
Type 12
1 pc(s).
53.863
54.5
94032080
4028177138896
EC002503
27180502

Approvals

© Rittal 2025 3

Approvals

Approvals	ATEX
	ATEX QA
	CQC-CCC
	IECEx
	IECEx QAR
	UL + C-UL (listed)
Explanations	Attestation of Conformity

© Rittal 2025