


Rittal – The System.

Faster – better – everywhere.



KEL 9304.000

Ex enclosures

State: 05/02/2026 (Source: rittal.com/uae-en)



FRIEDHELM LOH GROUP

KEL 9304.000 - Ex enclosures stainless steel, empty enclosure with screw-fastened cover

Ex enclosure with screw-fastened cover, stainless steel



Features

Model No.	KEL 9304.000
Design	Ex enclosures
Applications	<p>Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)</p>
Material	<p>Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal</p>
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Enclosure Cover
Dimensions	<p>Width: 300 mm Height: 200 mm Depth: 80 mm</p>
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)

Features

IP protection category to IEC 60
529 IP 66

Packs of 1 pc(s).

Net weight 2.4

Gross weight 2.44

Customs tariff number 94032080

EAN 4028177138605

ETIM 9 EC002503

ECLASS 8.0 27180502

Approvals

Approvals ATEX
ATEX QA
CQC-CCC
IECEx
IECEx QAR

Explanations Attestation of Conformity