Rittal – The System.

Faster - better - everywhere.





SV 9340.530 OM adaptors

State: 31/10/2025 (Source: rittal.com/uae-en)



SV 9340.530 - OM adaptors with spring terminals



Features

Model No.	SV 9340.530
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to- centre spacing	60 mm
Support rail type	Support frame, 1 x TS 45C
Number of poles	3-pole
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 6 mm²
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Packs of	1 pc(s).
Net weight	0.259
Gross weight	0.28

© Rittal 2025

Features

Copper weight (kg per piece)	0.027
Customs tariff number	85369095
EAN	4028177502628
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM adaptor 32 A

OM adaptor 32 A with tension spring clamp, 3-pole, for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications
Construction width: 45 mm

Length: 208 mm

Support frame: 45 x 170 mm Support frame support: -

PinBlock: -

Connector outlet: -

Support rail: 1 with anti-slip guard

System:

Rittal RiLine60

© Rittal 2025