

Rittal – The System.

Faster – better – everywhere.



RX 9360.000

RiLineX buying set

State: 03/07/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the 3-pole complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed VX enclosures, no drilling required.



Features

| | |
|--------------------------------------|--|
| Model No. | RX 9360.000 |
| Benefits | Time savings thanks to fully digital product data Reduced assembly time thanks to pre-assembled complete board Tested short-circuit resistance up to 65 kA Suitable for applications up to 1000 V AC and up to 1500 V DC Tested and certified to IEC and UL Simple extension and baying |
| Material | Upper part: Sheet steel, zinc-plated Contact plate: E-Cu, tin-plated Front cover: Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 35745 |
| Supply includes | 3 busbar connectors 1 front cover 1 insulating plate |
| IP protection category to IEC 60 529 | IP 2XB |
| Standards | IEC 61 439-1/-2 UL 508 |

Features

| | |
|---|--|
| Rated current max. | 780 A |
| Rated current (UL) | 780 A |
| Electrical ratings UL (SCCR) | 52.5 kA - 600 V, RMS, unprotected 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7 |
| Rated impulse withstand voltage U _{imp} | 12 kV |
| Rated voltage | 1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL) |
| Rated insulation voltage U _i | 1,000 V AC 1,500 V DC |
| Rated impulse withstand current | 103 kA 115.5 kA |
| Rated short-term withstand current/t | 45 kA/200 ms 52.5 kA/500 ms |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Number of poles | 3-pole |
| To fit Model No. | 9360004 9360008 9360024 9360028 9360064 9360068 9360084 9360088 |
| Fundamental frequency | 50...60 Hz |
| Ambient humidity (non- condensing) | 10...90 % |
| To fit busbars | 30 x 5/10 |

Features

| | |
|-------------------------------|---|
| Operating temperature range | -5 °C...55 °C |
| Dimensions | Width: 154 mm Height: 240 mm Depth: 77 mm |
| Fire load | 5.933 MJ/m ² |
| Packs of | 1 pc(s). |
| Net weight | 1.88 kg |
| Gross weight | 1.924 kg |
| Copper weight (kg per piece) | 0.297 |
| PCF per pack (cradle-to-gate) | 10.32 |
| Customs tariff number | 85369010 |
| ETIM 9 | EC002270 |
| Product description | RiLineX baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple, no-drill baying of boards between two bayed enclosures. Baying connectors are included with the supply. |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity PCF-declaration |

Tender text

RiLineX baying set for board

Baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and

contact hazard protection cover. For simple baying of boards between two bayed enclosures, no drilling required.

Tested short-circuit resistance up to 65 kA.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 30 mm x 5/10 mm

Rated current max.: 550/800 A

Dimensions: 154 mm x 240 mm x 77 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360000