Rittal – The System.

Faster – better – everywhere.





RX 9360.220 RiLineX connection adaptor

State: 19/10/2025 (Source: rittal.com/uae-en)



RX 9360.220 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.



Features

Model No.	RX 9360.220
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005
Rated current (UL)	400 A
Rated current of round conductor	450 A
Rated current of round conductor (UL)	400 A
Electrical ratings UL (SCCR)	27.5 kA - 600 V, RMS 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7
Cable outlet	Top/bottom
For bar systems with centre-to- centre spacing	60 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60

© Rittal 2025 2

Features

Dimensions	Width: 90 mm Height: 240 mm Depth: 95 mm
Connection of round conductors	10 - 150 mm²
Connection of round conductors, fine wire with wire end ferrule	16 - 150 mm²
Connection of round conductors, fine wire with AWG wire end ferrule	AWG 6 - AWG 250
Connection of round conductors, single-wire	10 - 16 mm²
Connection of round conductors, single-wire AWG	AWG 8 - AWG 6
Connection of round conductors, multi-wire	25 - 150 mm²
Connection of round conductors, multi-wire mm ²	AWG 250
Clamping area for laminated copper bars (W x H)	20 x 20 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage Uimp	12 kV
Rated insulation voltage	1,000 V

© Rittal 2025 3

Features

Power dissipation (max.)	19 W
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C
Ambient humidity (non- condensing)	1090 %
Packs of	1 pc(s).
Net weight	0.7
Gross weight	0.815
Customs tariff number	85369010
EAN	4028177997240
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025