Rittal – The System.

Faster – better – everywhere.





RX 9360.798 RiLineX component adaptor

State: 28/11/2025 (Source: rittal.com/uae-en)



RX 9360.798 - RiLineX component adaptor

RiLineX component adaptor (80 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar systems. With integral threaded inserts.



Features

Model No.	RX 9360.798
Design	With connection cable
Benefits	For mounting equipment for top hat rail installation, e.g. motor
	starter
	Pre-assembled connection cable
	Simple clip locking for support rails
	Optional anti-slip guard
	Snap-on mounting and simple adjustment for busbar thickness
	(5/10 mm)
	Simple assembly
	Coordinated accessories reduce the number of different items
	required
Material	Polyamide (PA 6)
	Fire protection corresponding to UL 94
Colour	RAL 9005
	RAL 35745
Connection cables (AWG)	AWG 4
Rated current of round conductor	80 A
Rated current of round conductor (UL)	80 A
<u> </u>	
Cable outlet	Тор

© Rittal 2025

Features

For bar systems with centre-to- centre spacing	60 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 72 mm Height: 239.4 mm Depth: 36.6 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C
Ambient humidity (non- condensing)	1090 %
Packs of	1 pc(s).
Net weight	0.7
Gross weight	0.702
Copper weight (kg per piece)	0.246
Customs tariff number	85369095
ETIM 9	EC001531

© Rittal 2025 3

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025