


# Rittal – The System.

Faster – better – everywhere.



## PK 9505.000

## Polycarbonate enclosures PK

State: 28/06/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9505.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | PK 9505.000   |
| Design                            | PK enclosure with solid cover   |
| Product description               | Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.  |
| Material                          | Enclosure: Fibreglass-reinforced polycarbonate<br>Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polyethylene |
| Colour                            | RAL 7035  |
| Supply includes                   | Enclosure with cover<br>Cover screws<br>Insulating bungs for wall mounting screws   |
| Protection category NEMA          | NEMA 4X   |
| Protection category to IEC 60 529 | IP 66   |
| IK Code                           | IK08  |

# Features

---

|                             |   |
|-----------------------------|---|
| Dimensions                  | Width: 94 mm<br>Height: 94 mm<br>Depth: 81 mm   |
| Operating temperature range | -35 °C...80 °C  |
| Basic material              | Polycarbonate   |
| Packs of                    | 6 pc(s).  |
| Net weight                  | 1.32 kg   |
| Gross weight                | 1.441 kg  |
| Customs tariff number       | 84879090  |
| ETIM 9                      | EC000261  |
| ECLASS 8.0                  | 27180101  |
| Product description         | PK Polycarbonate enclosure, WHD: 94x94x81 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover |

---

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | C-UL<br>DNV<br>UL<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity               |

---

# Tender text

Polycarbonate Housings without knockouts

Polycarbonate enclosure with solid cover without knockouts

Enclosure: Fibreglass-reinforced polycarbonate  
without knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate

all-round foamed-in PU seal  
Cover screws: Polyamide  
Insulating bungs: Polyethylene  
Supply includes: Cover screws  
Insulating bungs for wall mounting screws  
Accessories: Wall mounting bracket  
Protection category to IEC 60 529: IP 66  
Protection category NEMA: NEMA 4X  
Colour: similar to RAL 7035  
Dimensions (W x H x T): 94 x 94 x 81 mm