
Rittal – The System.

Faster – better – everywhere.



# KX 1541.000

# Terminal box KX, sheet steel, with gland plate

State: 19/11/2026 (Source: www.rittal.com/uk-en)

# KX 1541.000 - Terminal box KX, sheet steel, with gland plate

The small enclosure KX, terminal box KX, with a gland plate allows for flexible interior installation and simple cable entry with optimum use of space.







## Features

| | |
|---|---|
| Model No. | KX 1541.000 |
| Material | Enclosure: Sheet steel<br>Cover: Sheet steel, all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover<br>Mini cam locks<br>Sheet steel gland plates with seals and assembly parts |
| Dimensions | Width: 800 mm<br>Height: 400 mm<br>Depth: 120 mm |
| Protection category to IEC 60 529 | IP 55 |
| Protection category NEMA | NEMA 1<br>NEMA 12 |
| Type rating to 508A | Type 1<br>Type 12 |

© Rittal 2026

# Features

| | |
|---|---|
| IK Code | IK08 |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Gland plates | : 1 + 1<br>: 3 + 3 |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 10.541 kg |
| Gross weight | 11.65 kg |
| PCF per pack (cradle-to-gate) | 54.55 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 84879059 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | KX Terminal box, WHD: 800x400x120 mm, sheet steel, without mounting plate, with cover, with gland plate |

# Approvals

| | |
|---|---|
| Approvals | Bureau Veritas<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Certificates | Protection category |
| Explanations | Declaration of conformity<br>Declaration of conformity UK<br>PCF-declaration |