


# Rittal – The System.

Faster – better – everywhere.



## SV 9690.043

### Energy storage enclosure

State: 22/01/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9690.043 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fit-out. Ideal for efficient and modular energy storage installation with slide rails.

## Features

Model No.	SV 9690.043
Design	With flexible interior fit-out
Material	Enclosure frame: Sheet steel, 1.5 mm Roof plate: Sheet steel, 1.5 mm Door: Sheet steel, 1.5 mm Rear panel: Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Powder-coated, textured paint
Colour	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category to IEC 60 529	IP 20
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
PCF per pack (cradle-to-gate)	290.48 kg CO <sub>2</sub> eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177044319
ETIM 9	EC000261

## Approvals

# Approvals

---

Explanations

Declaration of conformity