Rittal – The System.

Faster – better – everywhere.



SZ 2411.621

Cable gland, polyamide

State: 19/11/2026 (Source: www.rittal.com/uk-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2411.621 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

Model No.	SZ 2411.621
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60 529	IP 68 (5 bar, 30 min)
Dimensions	Height: 28 mm
Thread	M20 x 1.5
Thread length	10 mm
Min. cable diameter	6 mm
Max. cable diameter	12 mm
Operating temperature range	-30 °C...100 °C
torque	5.5 Nm
Width across flats	24 mm
Dimensions	Thread: M20 x 1.5 Thread length: 10 mm
Type rating to 508A	Type 1 Type 4 Type 4X Type 12 Type 13
Packs of	50 pc(s).

© Rittal 2026

Features

Net weight	0.55 kg
Gross weight	0.615 kg
Customs tariff number	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, polyamide, size: M20x1,5, for cables ø 6-12 mm

Approvals

Approvals	CSA + CSAus UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2026