Rittal – The System.

Faster – better – everywhere.




# KX 1301.000

# E-Box KX

State: 19/11/2026 (Source: www.rittal.com/uk-en)

# KX 1301.000 - E-Box KX Stainless steel

The stainless steel E-Box KX provides user-friendly assembly as well as flexibility when choosing your lock system. The 180° hinges supplied as standard provide excellent accessibility to the enclosure interior.









## Features

| | |
|---|---|
| Model No. | KX 1301.000 |
| Product description | The stainless steel E-Box KX provides user-friendly assembly as well as flexibility when choosing your lock system. The 180° hinges supplied as standard provide excellent accessibility to the enclosure interior. |
| Material | Enclosure: Stainless steel<br>Door: Stainless steel, all-round foamed-in PU seal<br>Mounting plate: Sheet steel<br>Stainless steel 1.4404 (AISI 316L) |
| Surface finish | Enclosure and cover: Brushed, grain 180<br>Mounting plate: Zinc-plated |
| Supply includes | Mounting plate<br>Cam lock with 3 mm double-bit insert |
| Dimensions | Width: 200 mm<br>Height: 300 mm<br>Depth: 155 mm |
| Dimensions mounting plate (W x H) | 175 mm x 285 mm |
| Protection category to IEC 60 529 | IP 66 |

© Rittal 2026

# Features

| | |
|---|---|
| Type rating to 508A | Type 1<br>Type 3R<br>Type 3RX<br>Type 4<br>Type 4X<br>Type 12 |
| Material thickness - enclosure | 1.25 mm |
| Material thickness - door | 1.25 mm |
| Lock | Number of locks: 1<br>Material lock: Stainless steel 1.4404 (AISI 316L) |
| Basic material | Stainless steel 1.4404 (AISI 316L) |
| Packs of | 1 pc(s). |
| Net weight | 3.88 kg |
| Gross weight | 3.889 kg |
| PCF per pack (cradle-to-gate) | 13.5 |
| Customs tariff number | 84879059 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | KX E-Box, WHD: 200x300x155 mm, stainless steel 1.4404, with mounting plate, single-door, with cam lock |

# Approvals

| | |
|---|---|
| Approvals | Bureau Veritas<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>PCF-declaration |

# Tender text

Enclosure (E-Box, stainless steel)

Enclosure with door:
Stable stainless steel design,
body folded from a single piece and welded,
with protection channel all-round door opening,
with PE conductor connection in the enclosure,
solid rear panel with knockouts, door hinged on r/h side,
with foamed-in PU seal,
earthing in the door via bolt,
with cam lock with 3 mm double-bit insert to DIN 43668,
with mounting plate.
QR code:
QR code printed on body, cover and rating plate
for clear identification and easy retrieval of relevant
product information and documentation,
and for clear traceability of the individual parts.
Accessories: Top hat rail, wall mounting bracket,
Mini-comfort handle.
Material:
Enclosure, door: Stainless steel 1.4404 (AISI 316L)
Mounting plate: Sheet steel, zinc-plated
Enclosure and door surface finish:
Brushed, grain size 180
Protection category to IEC 60 529: IP 66
Protection category to UL 508A: Type 4X
Dimensions (W x H x D): 200x300x155 mm
Dimensions mounting plate (W x H): 175 x 285 mm

© Rittal 2026