



# Rittal – The System.

Faster – better – everywhere.



## SZ 2843.200 EMC cable glands

State: 24/08/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2843.200 - EMC cable glands

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

## Features

Model No.	SZ 2843.200
Design	Cable glands, metric
Product description	The cable sheathing may optionally be interrupted at the contact point or removed completely inside the enclosure. The cable shielding in the enclosure is retained. The supplied lock nut cuts automatically into the paint when screwed onto spray-finished enclosure surfaces, thus creating a conductive connection.
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Note	Minimum shield diameter = cable diameter less cable sheathing
Min. cable diameter	6 mm
Max. cable diameter	12 mm
Protection category IP69K	IP 69K
IP protection category to IEC 60529	IP 68
Shield diameter (min.)	5 mm
Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packs of	5 pc(s).
Net weight	0.17
Gross weight	0.2
Customs tariff number	73072980

# Features

EAN	4028177247031
E-Number Sweden	E1703717
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

# Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK