

Rittal – The System.

Faster – better – everywhere.



SK 3114.200

Digital enclosure internal temperature display and thermostat

State: 12/06/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3114.200 - Digital enclosure internal temperature display and thermostat

For installation in the enclosure door or wall.

Features

| | |
|-------------------------------------|--|
| Model No. | SK 3114.200 |
| Product description | For installation in the enclosure door or wall. |
| Technical specifications | Three-digit, 7-segment display Option of switching between °C/°F Includes 1800 mm long NTC sensor Two relay outputs as change-over contact and normally open contact (max. contact load 230 V, 6 A) Freely selectable switching difference |
| Colour | RAL 7035 |
| Packs of | 1 pc(s). |
| Operating temperature range | 0 °C...50 °C |
| Setting range | 5 °C...55 °C |
| Rated operating voltage | 100 V - 230 V, 1~, 50 Hz/60 Hz 24 V - 60 V (DC) |
| Storage temperature range | -20 °C...70 °C |
| IP protection category to IEC 60529 | IP 54 |
| Net weight | 0.258 kg |
| Gross weight | 0.259 kg |
| Customs tariff number | 90321020 |
| ETIM 9 | EC004587 |
| ETIM 8 | EC004587 |
| ECLASS 8.0 | 27210707 |

Features

| | |
|---------------------|---|
| Product description | SK Digital enclosure internal , temperature display and thermostat, 100-230 V, 1~, 50/60 Hz, 24-60 V (DC), Installation depth: 100 mm |
|---------------------|---|

Approvals

| | |
|--------------|---|
| Approvals | UR |
| Explanations | Declaration of conformity Declaration of conformity UK |