

# Rittal – The System.

Faster – better – everywhere.



## SK 3172.120 Pleated filter

State: 12/06/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3172.120 - Pleated filter for fan-and-filter units, roof-mounted fans, cooling units and chillers

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.



## Features

Model No.	SK 3172.120
Design	for filter fans / outlet filters
Material	PET
Colour	White
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3240.xxx 3241.xxx
Dimensions	Width: 212.5 mm Height: 212.5 mm Depth: 21 mm
Filter class	to DIN EN 779: G4 to DIN EN ISO 16890: ISO Coarse 70%
IP protection category to IEC 60529	IP 54 in fan-and-filter units/roof-mounted fans/outlet filters
Note on Model No.	No suitable for use in EMC filter fans.

# Features

---

Packs of	5 pc(s).
Net weight	0.335 kg
Gross weight	0.34 kg
Customs tariff number	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK Pleated filter IP54, for fan-and-filter units/outlet filters 3240./3241.xxx, WHD: 212.5x212.5x21 mm

# Approvals

---

Approvals	CSA UR + C-UR (recognized)
-----------	-------------------------------