Rittal – The System.

Faster – better – everywhere.




# KX 1565.000

# Terminal box KX

State: 19/11/2026 (Source: www.rittal.com/uk-en)

# KX 1565.000 - Terminal box KX Stainless steel

The stainless steel terminal box KX delivers maximum data quality and consistency of engineering while ensuring flexibility and reliability across a wide range of applications.


## Features

| | |
|---|---|
| Model No. | KX 1565.000 |
| Product description | The stainless steel terminal box KX delivers maximum data quality and consistency of engineering while ensuring flexibility and reliability across a wide range of applications. |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304)<br>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Brushed, grain 180 |
| Supply includes | Enclosure with cover<br>Quick-release fastener including plastic bushes |
| Dimensions | Width: 200 mm<br>Height: 200 mm<br>Depth: 120 mm |
| Protection category to IEC 60 529 | IP 66 |
| Protection category NEMA | NEMA 1<br>NEMA 3R<br>NEMA 3RX<br>NEMA 4<br>NEMA 4X<br>NEMA 12 |

© Rittal 2026

# Features

| | |
|---|---|
| Type rating to 508A | Type 1<br>Type 3R<br>Type 3RX<br>Type 4<br>Type 4X<br>Type 12 |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Lock | Number of locks: 4 |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Packs of | 1 pc(s). |
| Net weight | 1.934 kg |
| Gross weight | 2.131 kg |
| PCF per pack (cradle-to-gate) | 8.96 |
| Customs tariff number | 84879059 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | KX Terminal box, WHD: 200x200x120 mm, stainless steel 1.4301, without mounting plate, with cover, with quick-release fasteners |

# Approvals

| | |
|---|---|
| Approvals | Bureau Veritas<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>PCF-declaration |

# Tender text

Enclosure (terminal box, stainless steel)

Enclosure with cover:
Stable stainless steel design,
body folded from a single piece and welded,
with protection channel all-round cover opening,
Solid rear panel with knockouts,
cover with foamed-in PU seal,
with PE conductor connection in the enclosure,
earthing in the cover via bolt,
for quick and easy earthing,
with quick-release fastener.
QR code:
QR code printed on body, cover and rating plate
for clear identification and easy retrieval of relevant
product information and documentation,
and for clear traceability of the individual parts.
Accessories: Cover hinge,
mounting plate, top hat rail, wall mounting bracket,
mounting claw for second mounting level.
Material:
Enclosure, cover: Stainless steel 1.4301 (AISI 304)
Surface finish: Brushed, grain size 180
Protection category to IEC 60 529: IP 66
Protection category to UL 508A: Type 4X
Dimensions (W x H x D): 200x200x120 mm

© Rittal 2026