Rittal – The System.

Faster – better – everywhere.



SZ 2411.611

Cable gland, polyamide

State: 19/11/2026 (Source: www.rittal.com/uk-en)

SZ 2411.611 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

Model No.	SZ 2411.611
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60 529	IP 68 (5 bar, 30 min)
Dimensions	Height: 30 mm
Thread	M16 x 1.5
Thread length	10 mm
Min. cable diameter	5 mm
Max. cable diameter	10 mm
Operating temperature range	-30 °C...100 °C
torque	2.5 Nm
Width across flats	22 mm
Dimensions	Thread: M16 x 1.5 Thread length: 10 mm
Type rating to 508A	Type 4X
Packs of	50 pc(s).
Net weight	0.5 kg
Gross weight	0.546 kg

© Rittal 2026

Features

Customs tariff number	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, polyamide, size: M16x1,5, for cables ø 5-10 mm

Approvals

Approvals	CSA + CSAus UR UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK