

# Rittal – The System.

Faster – better – everywhere.



## AX 2744.010

### Operating panel

State: 23/07/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2744.010 - Operating panel for AX

For external mounting on an AE enclosure instead of a door and on surfaces. Frame construction with internal corner connectors, 3 mm aluminium plate secured from the inside.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | AX 2744.010   |
| Product description               | For external mounting on an AE enclosure instead of a door and on surfaces. Frame construction with internal corner connectors, 3 mm aluminium plate secured from the inside. |
| Material                          | Aluminium, natural anodised   |
| Supply includes                   | Aluminium frame<br>Display panel<br>Hinges<br>Brackets  |
| Protection category to IEC 60 529 | IP 54   |
| To fit Model No.                  | 1009.000<br>1039.000<br>1339.000  |
| Note                              | When installing instead of a door, the cam lock is required   |
| To fit                            | Enclosure type: AX<br>Width: = 600 mm<br>Height: = 380 mm   |
| Dimensions                        | Width: 597 mm<br>Height: 377 mm<br>Depth: 36 mm   |
| Dimensions of aluminium plate     | Width: 543 mm<br>Height: 323 mm   |
| Area available for population     | Width: 527 mm<br>Height: 307 mm   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 3.131   |

# Features

|                       |               |
|-----------------------|---------------|
| Gross weight          | 3.331         |
| Customs tariff number | 76169990      |
| EAN                   | 4028177938540 |
| ETIM 9                | EC000747      |
| ETIM 8                | EC000747      |
| ECLASS 8.0            | 27182204      |