

# Rittal – The System.

Faster – better – everywhere.



## SK 3108.100 Enclosure internal fan

State: 11/05/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3108.100 - Enclosure internal fan

To prevent hot-spots inside the enclosure and support the air routing of active enclosure climate control components.



## Features

|                         |                                                                                                                                                                                                                              |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.               | SK 3108.100                                                                                                                                                                                                                  |
| Product description     | To prevent hot-spots and support the air routing of active enclosure climate control components. Adjustable in two axes. Attached to the frame section. Several fans may be cascaded using the quick-release clamping strip. |
| Supply includes         | Complete unit with axial fan ready for connection<br>Snap-on pivot device<br>Assembly parts                                                                                                                                  |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz                                                                                                                                                                                                       |
| Power consumption Pel   | At 50 Hz: 19 W<br>At 60 Hz: 18 W                                                                                                                                                                                             |
| Rated current max.      | At 50 Hz: 0.12 A<br>At 60 Hz: 0.11 A                                                                                                                                                                                         |
| Packs of                | 1 pc(s).                                                                                                                                                                                                                     |
| Net weight              | 0.94 kg                                                                                                                                                                                                                      |
| Gross weight            | 1.126 kg                                                                                                                                                                                                                     |
| Customs tariff number   | 84145915                                                                                                                                                                                                                     |
| ETIM 9                  | EC000320                                                                                                                                                                                                                     |

# Features

---

|                     |                                                         |
|---------------------|---------------------------------------------------------|
| ETIM 8              | EC000320                                                |
| ECLASS 8.0          | 27180716                                                |
| Product description | SK enclosure internal fan, 19/18 W, 230 V, 1~, 50/60 Hz |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

---