

# Rittal – The System.

Faster – better – everywhere.



## SK 3138.000

## Roof-mounted fan, roof vent

State: 26/08/2025 (Source: [rittal.com/uk-en](https://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3138.000 - Roof-mounted fan, roof vent

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.



## Features

Model No.	SK 3138.000
Design	roof-mounted
Product description	Roof-mounted fan with a high protection category and flexible installation from the inside or outside.
Colour	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	without fan motor
Dimensions	Width: 400 mm Height: 133 mm Depth: 400 mm
Installation depth	27.5 mm
Mounting cut-out	Cut-out width: 258 mm Cut-out depth: 258 mm
IP protection category to IEC 60529	IP 21 without filter mat IP 54 including pleated filter

# Features

Protection category NEMA	NEMA 12
Note	<p>A chopped-fibre filter filter may optionally be used to increase the protection category to IP 55 (see accessories).</p> <p>To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays</p>
Operating temperature range	-20 °C...55 °C
Storage temperature range	-40 °C...70 °C
Packs of	1 pc(s).
Net weight	3.2
Gross weight	3.5
Customs tariff number	84145915
EAN	4028177709188
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

# Approvals

Approvals	<p>CSA</p> <p>UL + C-UL - FTTA</p> <p>UR + C-UR (recognized)</p>
Explanations	<p>Declaration of conformity</p> <p>Declaration of conformity UK</p>

# Tender text

Roof-mounted fan, roof vent

SK 3138.000

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories.

Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.

Colour: RAL 7035

Supply includes: Complete unit ready to install, including pleated filter

Fan: without fan motor

Dimensions (WxHxD): 400x133x400 mm

Mounting cut-out (WxD): 258x258 mm

Installation depth: 27.5 mm

IP protection category to IEC 60 529:

IP21 without filter mat, IP54 including pleated filter

Protection category NEMA: NEMA 12

Operating temperature range: -20 °C to 55 °C

Storage temperature range: -40 °C to 70 °C

Weight/pack: 3.2 kg