

Rittal – The System.

Faster – better – everywhere.



SK 3301.351 Connection hose

State: 19/07/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3301.351 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

Features

Model No.	SK 3301.351
Product description	1 m long (may be shortened), flexible, pressure-resistant connection hose, including screw connection on both sides with 1" internal thread/flat seal for connecting the LCP to existing pipework.
Length	1 m
Water connections	G 1" internal thread
Packs of	2 pc(s).
Net weight	2.5
Gross weight	3.04
Customs tariff number	84159000
EAN	4028177517608
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Tender text

Connection hose LCP Hybrid CW 10 kW / 20 kW,

DN 25 / PN 16

Model No. 3301.351

The flexible, pressure-resistant connection hose serves as a connection between an installed cold water supply system and the cold water connection of the LCP Hybrid 10 kW / 20 kW. The connection hose possesses flat-sealing unions with 1" internal thread and sealing gaskets on both ends. One of the unions is provided with a flange clamp to enable the hose to be cut to the required length.

Technical data:

Pack of: 2 pcs.

Length: 1 m

DN: 25 x 6mm

PN: 16

Min. bending radius: 150 mm

”””