

**Rittal – The System.**

Faster – better – everywhere.



**SK 3237.067**

**Chopped-fibre filter mat**

State: 11/09/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3237.067 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.



## Features

|                     |  |
|---------------------|--|
| Model No.           | SK 3237.067  |
| Design              | for EMC filter fans  |
| Product description | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material            | Copper-nickel-chrome coated chemical fibres  |
| Colour              | Anthracite   |
| Note                | Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.  |
| To fit Model No.    | 3237.4xx/3237.8xx  |
| Dimensions          | Width: 92 mm<br>Height: 92 mm<br>Depth: 10 mm  |
| Filter class        | to DIN EN 779: G2<br>to DIN EN ISO 16890: ISO Coarse 50%   |
| Packs of            | 5 pc(s).   |
| Net weight          | 0.005  |

# Features

|                       |               |
|-----------------------|---------------|
| Gross weight          | 0.01          |
| Customs tariff number | 56039390      |
| EAN                   | 4028177028661 |
| ETIM 9                | EC002513      |
| ETIM 8                | EC002513      |
| ECLASS 8.0            | 27180706      |

# Approvals

|              |                        |
|--------------|------------------------|
| Approvals    | UR + C-UR (recognized) |
| Certificates | EAC                    |