

Rittal – The System.

Faster – better – everywhere.



SK 3328.544

TopTherm wall-mounted cooling unit Blue e, NEMA 4X

State: 28/06/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3328.544 - TopTherm wall-mounted cooling unit

Blue e, NEMA 4X 0.5 - 2.5 kW

Energy-efficient Blue e wall-mounted cooling units in power categories 500 W to 2,500 W with e-Comfort controller integrated as standard and electrical condensate evaporation. Protection category NEMA 4X.



Features

| | |
|---------------------|---|
| Model No. | SK 3328.544 |
| Design | wall-mounted |
| Product description | Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. Protection category NEMA 4X. |
| Benefits | May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller |
| Material | Stainless steel 1.4404 (AISI 316L) |
| Colour | RAL 7001 |
| Supply includes | Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts Integral electric condensate evaporation |

Features

| | |
|--|---|
| Total cooling output to DIN EN 14511 | Cooling output L35 L35/50 Hz: 2.05 kW Cooling output L35 L35/60 Hz: 2.25 kW Cooling output L35 L50/50 Hz: 1.35 kW Cooling output L35 L50/60 Hz: 1.5 kW |
| Rated operating voltage | 400 V, 3~, 50 Hz 460 V, 3~, 60 Hz |
| Rated current max. | At 50 Hz: 2.2 A At 60 Hz: 2.4 A |
| Start-up current max. | At 50 Hz: 4.8 A At 60 Hz: 5.5 A |
| Air throughput (unimpeded air flow) | External circuit: 900 m ³ /h Internal circuit: 900 m ³ /h |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 2.25 Refrigeration factor L35 L35 (EER) 60 Hz: 1.95 |
| Design | wall-mounted |
| Dimensions | Width: 405 mm Height: 1,650 mm Depth: 388 mm |
| Protection category to IEC 60 529 | External circuit IP 34 Internal circuit IP 55 |
| Protection category NEMA | NEMA 4X |
| Refrigerant/cooling medium | Refrigerant: R-513A Quantity: 0.9 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.57 t |
| Temperature control | e-Comfort controller (factory setting +35 °C) |
| Operating temperature range | 10 °C...50 °C |
| Storage temperature range | -40 °C...70 °C |
| Setting range | 20 °C...50 °C |
| Power consumption Pel | Power consumption L35 L35/50 Hz: 0.92 kW Power consumption L35 L35/60 Hz: 1.15 kW Power consumption L35 L50/50 Hz: 1.15 kW Power consumption L35 L50/60 Hz: 1.3 kW |

Features

| | |
|--|---|
| Permissible operating pressure (p. max.) | 28 bar |
| Pre-fuse | Motor circuit-breaker: 6.3...10 A |
| Packs of | 1 pc(s). |
| Net weight | 91.5 kg |
| Gross weight | 95 kg |
| Customs tariff number | 84158200 |
| ETIM 9 | EC000855 |
| ETIM 8 | EC000855 |
| ECLASS 8.0 | 27180704 |
| Product description | SK cooling unit Blue e, wall-mounted, NEMA 4X, 2.2 kW, 400-460 V, 3~, 50/60 Hz, Stainless steel, WHD: 405 x 1650 x 388 mm |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) UL + C-UL - FTFA UR + C-UR (recognized) |
| Explanations | FCC Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK |