

Rittal – The System.

Faster – better – everywhere.



SK 3313.420 Liquid Cooling Package

State: 9/07/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3313.420 - Liquid Cooling Package LCP rack DX, LCP rack DX/FC

Rack-based cooling on one to two IT racks. Continuous cooling output adjustment due to the use of an output-controlled compressor in the LCP Rack DX (evaporator) An external condenser is required to operate the unit.



Features

| | |
|--------------|---|
| Model No. | SK 3313.420 |
| Design | DX |
| Benefits | <ul style="list-style-type: none">Maximum energy efficiency due to EC fan technology and IT-based controlMinimal pressure loss at the air end, which in turn minimises the power consumption of the fansControl of the server inlet temperatureThanks to the speed-regulated compressor, the cooling output is ideally adapted to actual requirementsWith redundant temperature sensor integrated at the air end as standardSpecific maintenance of the LCP DX due to separation of cooling and server racks |
| Applications | <ul style="list-style-type: none">Ideal for IT cooling of small and medium-sized locationsOne or two racks can be cooled separately |

Features

| | |
|--|---|
| Function principle | The LCP draws in the air at the sides at the rear of the server enclosures, cools it using high-performance compact impellers, and blows the cooled air back into the front part of the server enclosure at the sides Absorbed thermal energy is emitted to the ambient air at the external condenser location, without heating up the installation room |
| Material | Sheet steel, spray-finished |
| Colour | RAL 7035 |
| Options | Humidifier Dehumidification and reheater Condensate drain pump Low-temperature/high-temperature condenser (-40 °C/+53 °C) |
| Design | Rack cooling |
| Monitoring | Direct connection of the unit via SNMP over Ethernet Integration into RiZone |
| Total cooling output to DIN EN 14511 | Useful cooling output L22 L35: 12 kW Useful cooling output L22 L45: 10 kW |
| Total cooling output/Number of fan modules | 12 kW/4 |
| Total cooling output | 12 kW |
| Modulation range | 3 - 12 kW |
| Air throughput (unimpeded air flow) | At 50 Hz: 4,800 m ³ /h |
| Dimensions | Width: 300 mm Height: 2,000 mm Depth: 1,200 mm |
| To fit enclosure type | VX IT |
| Installation in bayed enclosure suite | Flush |
| Rated operating voltage | 380 V - 480 V, 3~, 50 Hz/60 Hz |
| Rated current max. | At 50 Hz: 7.5 A |

Features

| | |
|---|--|
| Max. cooling output | 12 kW |
| Type of electrical connection | Connection clamp |
| Duty cycle | 100 % |
| EC fan | Yes |
| SNMP card | Yes |
| Fans may be exchanged with the system operational | Yes |
| Temperature control | Linear fan control Inverter-controlled compressor |
| Pre-fuse | Miniature circuit-breaker/fuse: 20 A |
| Storage temperature range | -20 °C...50 °C |
| Operating temperature range | 5 °C...35 °C |
| Noise level | At 50 Hz: 68 dB(A) |
| Protection category to IEC 60 529 | IP 40 |
| Options | Humidifier Dehumidification and reheater Condensate drain pump Low-temperature/high-temperature condenser (-40 °C/+53 °C) |
| Packs of | 1 pc(s). |
| Net weight | 213 kg |
| Gross weight | 224 kg |
| Customs tariff number | 84186900 |
| ETIM 9 | EC002515 |
| ETIM 8 | EC002515 |
| ECLASS 8.0 | 27180712 |
| Product description | LCP Rack DX, 12 kW, flush, RAL 7035, WHD: 300 x 2000 x 1200 mm, 380 – 480 V/3~/50 – 60 Hz |

Approvals

Explanations

Declaration of conformity

Tender text

LCP Rack DX, 3313.420 WHD (mm) 300x2000x1200

IT-optimised design, providing ideal support for "front-to-back" air routing for the 482.6 mm (19") installations.

As a direct condenser, the integrated air/refrigerant heat exchanger guarantees a cooling output of up to 12 kW with standard server enclosure dimensions, the lowest possible weight, and comprehensive possibilities for monitoring.

The LCP Rack DX is mounted on the side of the rack, with which it then forms a closed system.

The warm server air is drawn in directly from the rear of the rack and the cooled air is blown back in front of the 19" equipment level from the side, over the whole height of the enclosure.

The LCP Rack DX is closed up to the server rack at the front and rear and there forms a flush joint with the rack.

The LCP Rack DX can be used to cool either one or two server racks.

In its maximum configuration, the unit is equipped with four EC fans, for maximum efficiency and minimum power consumption.

The flow characteristics of the heat exchanger are optimised for the lowest possible pressure losses on the air side. This minimises the energy consumption of the fans.

An integrated inverter with corresponding controller serves to regulate the speed of the installed compressor.

This permits stepless adaptation of the output, also in partial-load operation, and by reducing energy consumption also achieves a reduction in operating costs.

Alongside the compressor, the cooling circuit of the LCP Rack DX comprises a collecting tank, liquid separator, electronic expansion valve, optimised heat exchanger, high and low-pressure sensors, Schrader valves, filter dryer, non-return valve, high-pressure switch and shut-off devices.

The refrigerant connections and the electrical power connection to the unit can be realised from above or below.

The system comprising LCP Rack DX and external condenser must be filled with refrigerant R410A after installation at the site.

The LCP Rack DX and the server rack remain separate from each other. This simplifies assembly and service work and excludes the need for unwanted access to the server rack for maintenance purposes. Maintenance and service for all relevant components can be realised quickly and simply thanks to the optimised layout. The fans can be exchanged quickly and at any time, even while the system is operational (hot swapping). The fans are installed in the cold air section, which increases their service life.

Condensate management is integrated into the unit. Any condensate is collected in a collecting tray in the base and from there discharged to the outside via a hose.

Thanks to the integrated controller, the LCP Rack DX operates fully autonomously. The setpoint is the server intake air temperature, which is automatically held constant at the set value. Three sensors are present in each case for detection of the cold and warm air temperatures, providing for the appropriate redundancy.

Monitoring and alarm management for all physical parameters is realised via SNMP and Ethernet. The SNMP card is integrated as standard in the electrical box, already connected to the main board.

A display with operating keys is integrated on the front of the unit to display and set the physical parameters.

The external condenser SK 3311.360 is needed to operate the LCP Rack DX. Installation and commissioning on site, laying of the refrigerant pipes, and evacuation and filling of the system with refrigerant are not included in the scope of supply and must be realised by correspondingly qualified persons.

Technical specifications:

Useful cooling output:

12 kW at 35 °C ambient temperature at place of installation of the condenser

10 kW at 45 °C ambient temperature at place of installation of the condenser

Installed fans: 4

Air throughput: max. 4,800 m³/h

Intake temperature, set: 22 °C

Connection, liquid side: 12 mm, external thread

Connection, gas intake side: 12 mm, external thread

Power supply: 400 V, 3~, N, PE, 50/ 60 Hz (voltage range 380-480 V)

Max. connected load: 4,700 W

Refrigerant: R410A

Connection length, max.: 45 m

Height difference (condenser higher/lower), max: 20/3 m

Dimensions (WxHxD): 300 x 2000 x 1200 mm

Weight: 201 kg

Colour: RAL 7035

Integrated SNMP card for network connection

Option on application:

Humidifier

Dehumidification + heater

Condensate pump

High temperature condenser (up to +53°C)

Low temperature condenser + winter kit (down to -40°C)

Needed accessories:

3311.360 Air cooled condenser for 3313.420 (-20°C to +45°C)