

Rittal – The System.

Faster – better – everywhere.



SK 3313.614 Connection hose

State: 11/09/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3313.614 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

Features

Model No.	SK 3313.614
Design	Rack cooling CW
Product description	The LCU cooling water connection is easily connected to the on-site pipework with the water connection kit. The hoses have a 90° bend on one side and a clamping tray on the other, to allow shortening of the hoses. Allows shortening of the hoses.
Material	NBR (internal) with steel spiral and fabric inlay
Length	2.5 m
Water connections	G ¾" internal thread
Operating temperature range	-30 °C...70 °C
Permissible operating pressure (p. max.)	10 bar
Packs of	2 pc(s).
Net weight	5.08
Gross weight	5.485
Customs tariff number	85444290
EAN	4028177983861
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712