

**Rittal – The System.**

Faster – better – everywhere.



**SV 3528.010**

**PLS special busbars E-Cu**

State: 29/01/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3528.010 - PLS special busbars E-Cu

Lengths range from 495 mm to 2400 mm.



## Features

Model No.	SV 3528.010
Material	E-Cu
Bar thickness	10 mm
Cross-section	900 mm <sup>2</sup>
Note	May be cut individually to required length
Busbar type	Busbar E-Cu
To fit busbar system	PLS 1600
To fit Model No.	9342.000 9342.004 9342.050
Dimensions	Length: 895 mm
To fit	Width: = 1,000 mm
Packs of	3 pc(s).
Net weight	21.72

# Features

---

Gross weight	21.72
Copper weight (kg per piece)	7.24
Customs tariff number	74071000
EAN	4028177504011
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

# Tender text

PLS 1600 special busbars  
PLS 1600 special busbars E-Cu  
Technical specifications  
Length: 895 mm  
Bar thickness: 10 mm  
Cross section: 900 qmm  
Weight: 8.01 Kg/m  
Electrical parameters  
IEC: to 1600 A  
UL 508: 1400 A  
System:  
Rittal RiLine60