

# Rittal – The System.

Faster – better – everywhere.



## SV 3569.005 Laminated copper bars

State: 18/08/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3569.005 - Laminated copper bars

Cu lamina made of high-purity electrolyte copper 720, length: 2000 mm/bar.



## Features

Model No.	SV 3569.005
Material	Cu lamina High-purity electrolyte copper F20 Insulation: Highly resistant vinyl compound, elongation 370%, temperature: -30 °C...+105 °C, fire protection corresponding to UL-94 V0, dielectric strength: 20 kV/mm
Length	2,000 mm
Rated current for temperature increase 50 K	480 A
Rated current for temperature increase 30 K	365 A
Rated current for temperature increase 70 K	575 A
Note	Construction = Number of lamina x lamina width x lamina thickness May be cut individually to required length The conductor temperature of the laminated copper bar is derived by adding the ambient temperature and the temperature increase together. Example: 3565.005 carrying 180 A, i.e. the temperature increases by 30 K. At an ambient temperature of 35 °C, this produces a resultant conductor temperature of 35 °C + 30 K = 65 °C.

## Features

Version – laminated flat copper	Number of lamina: 10 Membrane width: 15.5 mm Membrane thickness: 0.8 mm
Packs of	1 pc(s).
Net weight	2.467
Gross weight	2.66
Copper weight (kg per piece)	2.21
Customs tariff number	74071000
EAN	4028177666757
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

## Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK