

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.062 Command panel HD

State: 28/06/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.062 - Command panel HD

Monitors, PCs and other components with displays are hygienically and securely protected in the command panel. The roof tilt of 30° prevents objects from being deposited on it, and allows liquids to run off quickly.

## Features

|                                |   |
|--------------------------------|---|
| Model No.                      | HD 4000.062   |
| Benefits                       | Roof angled forwards by 30°<br>Height-adjustable mounting plate for screen up to 24"<br>Holder for desktop TFT, height-adjustable for screens up to 24"   |
| Material                       | Enclosure and door: Stainless steel 1.4301 (AISI 304)<br>Lock insert HD: Stainless steel 1.4404 (AISI 316L)<br>Viewing window: Polycarbonate<br>Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600<br>Viewing window: Polycarbonate |
| Surface finish                 | Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm<br>Seal: Blue, dyed (RAL 5010)   |
| Supply includes                | Enclosure of all-round solid construction<br>Door with viewing window and inserted seal<br>R/h door hinge<br>Holder for desktop TFT with VESA 75/100 locator  |
| Options                        | without viewing window<br>Mounting panel instead of a mounting plate<br>Cut-out for touch panel instead of viewing window<br>HD keyboard support  |
| Dimensions                     | Width: 810 mm<br>Height, front: 692 mm<br>Height rear: 848 mm<br>Depth: 266 mm  |
| Visible area                   | Viewing window width: 535 mm<br>Viewing window height: 325 mm   |
| Material thickness - enclosure | 1.5 mm  |

# Features

---

|                               |          |
|-------------------------------|----------|
| Material thickness - door     | 2 mm     |
| Protection category NEMA      | NEMA 4X  |
| IK Code                       | IK08     |
| Packs of                      | 1 pc(s). |
| Net weight                    | 33.2 kg  |
| Gross weight                  | 33.2 kg  |
| PCF per pack (cradle-to-gate) | 99.56    |
| Customs tariff number         | 94032080 |
| ETIM 9                        | EC000261 |
| ETIM 8                        | EC000261 |
| ECLASS 8.0                    | 27180101 |

# Approvals

---

|              |                 |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|