


Rittal – The System.

Faster – better – everywhere.



SV 3586.020 CUPONAL busbars

State: 4/09/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3586.020 - CUPONAL busbars

Copper-coated aluminium busbar



Features

Model No.	SV 3586.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Length	2,400 mm
Rated current max.	493 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	30 mm x 10 mm
Dimensions	Length: 2,400 mm
Packs of	3 pc(s).
Net weight	26.85
Copper weight (kg per piece)	2.61
Customs tariff number	74071000

Features

EAN	4028177686588
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---