

Rittal – The System.

Faster – better – everywhere.



AS 4050.150 Assembly frame

State: 8/12/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.150 - Assembly frame

The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.

Features

Model No.	AS 4050.150
Design	150 MN (manually tilt-adjustable)
Product description	The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.
Benefits	For ergonomic, back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimum space requirements during non-use Simple handling due to four castors including total lock function Variable mounting plate attachment with a quick-release fastener
Technical specifications	Tilt adjustment approx. 0 – 80°
Supply includes	Assembly frame 1 clamping unit pack, bottom 1 clamping unit pack, top
Note	With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved.
Machine dimensions	Width: 1,400 mm Depth: 1,250 mm
Dimensions support surface max.	Width: 1,110 mm Height: 1,900 mm
Dimensions support surface min.	Width: 1,110 mm Height: 1,230 mm
Load capacity	150 kg
Working height	Working height (min.): 100 cm Working height (max.): 100 cm
Packs of	1 pc(s).

Features

Net weight	123
Gross weight	138
Customs tariff number	84279000
EAN	4028177804609
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	36659090

Approvals

Explanations	Declaration of conformity
--------------	---------------------------