


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.454

## Crimping machine R8 E

State: 26/08/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.454 - Crimping machine R8 E

Electrically driven wire stripping and crimping machine for taped wire end ferrules on a reel.



## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4050.454  |
| Design                   | Touchscreen display  |
| Product description      | Electrically powered wire stripping and crimping machine for taped wire end ferrules on a reel.                                |
| Benefits                 | Easy to operate<br>Fast adjustment<br>Flexible use in the workshop<br>Rapid replacement of consumables                         |
| Technical specifications | Crimping range 0.5 - 2.5 mm <sup>2</sup> (AWG 20 - 14)<br>Crimping length 8 mm (0.31 in.)<br>Insertion length 40 mm (1.57 in.) |
| Note                     | The standard crimping form is trapezoid – others available on request  |
| Dimensions               | Width: 288 mm<br>Height: 230 mm<br>Depth: 345 mm   |
| Rated operating voltage  | 100 V - 240 V, 1~, 50 Hz/60 Hz   |
| Apparent power           | 100 VA   |
| Compression              | Trapezoid crimp  |
| Cycle time               | 1.8 s  |
| Packs of                 | 1 pc(s).   |

# Features

|                       |               |
|-----------------------|---------------|
| Net weight            | 16            |
| Gross weight          | 16            |
| Customs tariff number | 84798997      |
| EAN                   | 4028177813465 |
| ETIM 9                | EC002778      |
| ETIM 8                | EC002778      |
| ECLASS 8.0            | 36600890      |