

**Rittal – The System.**

Faster – better – everywhere.



**VX 5301.330**

**Gland plate modules, vented**

State: 10/06/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.330 - Gland plate modules, vented for VX IT

For closing the base

## Features

|                               |   |
|-------------------------------|---|
| Model No.                     | VX 5301.330   |
| Product description           | For closing the base  |
| Benefits                      | Large perforated section to support passive climate control of the enclosure<br>Filter mat slides in from above for easy replacement  |
| Material                      | Sheet steel   |
| Surface finish                | Zinc-plated   |
| Supply includes               | Gland plate modules, vented<br>Filter mat<br>Assembly parts   |
| Assembly instruction          | Several gland module plates must be combined to seal the base completely in the VX IT<br>The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm. |
| Dimensions                    | Depth: 237.5 mm   |
| To fit                        | Enclosure type: VX IT<br>Width: = 600 mm  |
| Packs of                      | 1 pc(s).  |
| Net weight                    | 1.44 kg   |
| Gross weight                  | 1.64 kg   |
| PCF per pack (cradle-to-gate) | 6.2 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared  |
| Customs tariff number         | 94039910  |
| ETIM 9                        | EC002620  |
| ECLASS 8.0                    | 27189261  |

# Features

---

Product description

VX IT gland plate module, ventilated, for width 600 mm, W x D 600 x 237.5 mm, sheet steel