

Rittal – The System.

Faster – better – everywhere.



VX 5301.516

Castor module

State: 17/04/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.516 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

Features

| | |
|-----------------------|---|
| Model No. | VX 5301.516 |
| Supply includes | 1 transport module with 2 castors 1 transport module with 2 castors, fixed Assembly parts |
| Dimensions | Width: 556 mm Height: 82.5 mm Depth: 203 mm |
| Assembly instruction | The base area must be open at the mounting points |
| To fit | Enclosure type: VX: = 600 mm Enclosure type: VX IT |
| Load capacity | Max. admissible load: Static 15,000 N Max. admissible load: Dynamic 10,000 N |
| Note | The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground. |
| Packs of | 1 pc(s). |
| Net weight | 10 kg |
| Gross weight | 10.3 kg |
| Customs tariff number | 83024900 |
| ETIM 9 | EC002621 |
| ECLASS 8.0 | 27189262 |
| Product description | Castor module for VX IT, for W: 600 mm, for easy movement directly at the point of use, for mounting directly on the enclosure. |

Tender text

Castor module for W: 600 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts