

# Rittal – The System.

Faster – better – everywhere.



## DK 5302.005

### Air baffle plate

State: 3/08/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5302.005 - Air baffle plate for VX IT 482.6 mm (19") mounting angles, dynamic

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

|                     |   |
|---------------------|---|
| Model No.           | DK 5302.005   |
| Product description | For selectively boosting the energy efficiency of a climate control system.   |
| Benefits            | Vertical brush strip for collision-free shielding with installed rail systems on the outer mounting level.  |
| Applications        | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.  |
| Material            | Sheet steel<br>Blanking panel: Plastic, UL 94-HB, halogen-free<br>Brush strip: Plastic, UL 94-HB  |
| Surface finish      | Spray-finished  |
| Colour              | RAL 9005  |
| Supply includes     | 2 vertical trim panels<br>2 horizontal trim panels<br>4 brush strips<br>4 cellular PU foam pieces<br>Assembly parts<br>6 blanking panels, 482.6 mm (19"), 1 U |

# Features

|                               |  |
|-------------------------------|--|
| Assembly instruction          | <p>The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning.</p> <p>The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles.</p> <p>482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.</p> |
| To fit                        | <p>Width: = 800 mm</p> <p>Height: = 2,000 mm</p>   |
| Packs of                      | 1 pc(s).   |
| Net weight                    | 7.7  |
| Gross weight                  | 8.12   |
| PCF per pack (cradle-to-gate) | 30.9 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared   |
| Customs tariff number         | 73269098   |
| EAN                           | 4028177955202  |
| E-Number Sweden               | E7282577   |
| ETIM 9                        | EC000331   |
| ECLASS 8.0                    | 27189272   |