

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.143**

**Splitter hole punch, round**

State: 7/12/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.143 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

## Features

|  |   |
|--|---|
| Model No.  | AS 4055.143   |
| Design   | With triple splitting   |
| Product description                                    | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes  | Female dies<br>Male dies  |
| Machinable material                                    | Stainless steel   |
| Maximum machinable material thickness, stainless steel | 2.5 mm  |
| Ø punch  | 43.2 mm   |
| Note   | When operating with wrenches, tension screws with ball bearings should be used.           |
| Suitable for hydraulic bolt order number               | 4055.663  |
| Tension screw (Ø x L)                                  | 19 x 75 mm  |
| Hydraulic tension screw Ø                              | 19 mm   |
| Packs of   | 1 pc(s).  |
| Net weight   | 0.454   |
| Gross weight   | 0.486   |
| Customs tariff number                                  | 82073010  |
| EAN  | 4028177808096   |
| ETIM 9   | EC000156  |
| ETIM 8   | EC000156  |

# Features

---

ECLASS 8.0

21049047