

Rittal – The System.

Faster – better – everywhere.



AS 4055.512

Splitter hole punch, round

State: 19/06/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.512 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.512
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	1.5 mm
Ø punch	12.5 mm
For threads	M12
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.660
Tension screw (Ø x L)	6 x 40 mm
Hydraulic tension screw Ø	6 mm 19 mm
Packs of	1 pc(s).
Net weight	0.034 kg
Gross weight	0.049 kg
Customs tariff number	82073010
ETIM 9	EC000156

Features

ETIM 8	EC000156
ECLASS 8.0	21049047
Product description	Splitter hole punch, round for sheet steel, with triple splitting
